

The best in fuel cell and metal hydride technology



- RELIABLE FUEL CELLS FROM 12W 30W
- REFILLABLE HYDROGEN CARTRIDGES
- ON DEMAND DESKTOP HYDROGEN REFULEING
- O SOME OF THE MOST EFFICIENT FUEL CELLS ON THE MARKET

Fuel Cells





H-12 12W

FCS-B12

| 0 | Integrated fan and casing |
|---|---------------------------|

Type of fuel cell PEM Number of cells 13 Rated power 12W Rated performance 7.8V@1.5A Purging valve voltage 6V Blower voltage 5V Reactants Hydrogen and Air Ambient temperature 5-30°C (41-86°F) Max stack temperature 55°C(131°F) Hydrogen pressure 0.45-0.55Bar Humidification Self-humidified Cooling Air (integrated cooling fan) $\textbf{Stack weight (with fan \& casing)} \quad 275g(\pm 30g)$ Controller weight 90g(±10g) Stack size 75x47x70mm Flow rate at max output 0.18L/min Hydrogen purity ≥99.995% dry H₂ Start up time ≤30s (ambient temp.) Efficiency of system 40% at full power





H-20 20W

FCS-B20

Controller




- Miniature electronic valve
- O Control electronics
- ntegrated fan and casing
- O Low voltage protection
- 20W stack with blower

| Type of fuel cell | PEM |
|----------------------------------|------------------------------|
| Number of cells | 13 |
| Rated power | 20W |
| Rated performance | 7.8V@2.6A |
| Purging valve voltage | 6V |
| Blowervoltage | 5V |
| Reactants | Hydrogen and Air |
| Ambient temperature | 5-30°C (41-86°F) |
| Max stack temperature | 55°C(131°F) |
| Hydrogen pressure | 0.45-0.55Bar |
| Humidification | Self-humidified |
| Cooling | Air (integrated cooling fan) |
| Stack weight (with fan & casing) | 275g(±30g) |
| Controller weight | 90g(±10g) |
| Stack size | 75x47x70mm |
| Flow rate at max output | 0.28L/min |
| Hydrogen purity | ≥99.995% dry H ₂ |
| Start up time | ≤30s (ambient temp.) |

Efficiency of system

| | | H-20 | U-I Curve | | |
|----|-----|------|-----------|-----|------------|
| | ٧ | 1120 | O I Ouive | | |
| 14 | Т | | | | |
| 12 | | | | | |
| 10 | + | | | | |
| 8 | +- | | | | |
| 6 | +- | | | | |
| 4 | +- | | | | |
| 2 | +- | | | | |
| 0 | ₩ | - | - | | — <i>1</i> |
| | 0.0 | 1.0 | 2.0 | 3.0 | 4.0 |
| | | H-20 | P-I Curve | | |



H-30 30W

FCS-B30







- Controller
 - Miniature electronic valve
 - Control electronics

| Type of fuel cell | PEM |
|----------------------------------|------------------------------|
| Number of cells | 14 |
| Rated power | 30W |
| Rated performance | 8.4V@3.6A |
| Purging valve voltage | 6V |
| Blower voltage | 5V |
| Reactants | Hydrogen and Air |
| Ambient temperature | 5-30°C (41-86°F) |
| Max stack temperature | 55°C(131°F) |
| Hydrogen pressure | 0.45-0.55Bar |
| Humidification | Self-humidified |
| Cooling | Air (integrated cooling fan) |
| Stack weight (with fan & casing) | 280g(±30g) |
| Controller weight | 90g(±10g) |
| Stack size | 80x47x75mm |
| Flow rate at max output | 0.42L/min |
| Hydrogen purity | ≥99.995% dry H ₂ |
| Start up time | ≤30s (ambient temp.) |
| Efficiency of system | 40% at full power |
| | |

40% at full power





Hydrogen Generation and Storage



Hydrogen on demand for universities and schools



The world's only on demand hydrogen supply system for refilling HYDROSTIK PRO metal hydride cartridges. By generating hydrogen through water electrolysis, HYDROFILL PRO enables homes and classrooms to become energy self-sufficient. Then, rather than compressing hydrogen gas, the safe and reliable HYDROSTIK PRO binds hydrogen with a metal alloy to form a solid metal hydride. Perfect for next generation science kits and engineering projects.

| HYDROFILL RPO | Stack type | PEM electrolysis cell |
|---------------|------------------------|--------------------------------|
| | Dimensions (WxDxH) | 145x153x208 mm (5.7x 6x8.2 in) |
| | Weight | 1.8Kg ±5% (3.97Lbs ±5%) |
| | Rated power | ≤23W |
| | Input voltage | DC: 10V-19V |
| | Waterinput | De-ionized or distilled water |
| | Water temperature | 10-40°C (50-104°F) |
| | Water consumption | Approx. 20ml/hr (1.2in3 /hr) |
| FCH-020 | H2 output pressure | 0-3.0 MPaG (0-435.11 PSI) |
| | H2 generation capacity | Up to 3L/hr (0-183 in /hr) |
| | Purity | 99.995% |
| | Compatible cartridge | HYDROSTIK & HYDROSTIK PRO |
| | Refilling time for one | Around 4 hours |
| | Cartridge | (at 25°C room temperature) |
| | | |

| HYDROSTIK RPO | Name | HYDROSTIK PRO |
|---------------|-------------------------|-------------------|
| | Model number | LWH22-10L-5 |
| | Capacity | 10 L hydrogen |
| | Hydrogen purity | ≧99.995% |
| 목 | Cartridge size | ø22x88mm |
| | Weight | Approx. 105g |
| 2 | Storage material | AB5 metal hydride |
| .WH22-10L-5 | Rated charging pressure | 3.0MPa |
| 3 | Working temperature | 0-55°C (0-131°F) |
| | Service life | 10 years |

Refueling Tools



REFILLING TREE

21-RT-21



- O Charge up to 21 Hydrostiks at once
- M6 screws provided to block surplus holes
- Takes up to 1h to charge all 21
- Dual headed pressure regulator required but not included.

REFUELING TUBING CONNECTOR



- Enables single Hydrostiks to be refilledfrom large cannister
- Connects to Refueling Tubing

HOW IT WORKS

REFUELING TUBING

FSC-RA-5

350L



- O Connects Refilling Tree (or single Hydrostik) to hydrogen cannister
- Also used to check leakages from cartridges

SINGLE REFILLING ADOPTER

FSC-RA-1



- Facilitates Hydrostik recharging from small hydrogen cannister
- O Connects to silicon tubing

IOW IT WORKS

1-STEP PRESSURE REGULATOR

FSC-PR-1

HOW IT WORKS



- Facilitates release of hydrogen from Hydrostik
- O Connects to silicon tubing

SILICON TUBING

FCEA-14



- O Connects Single Refilling Adopter to small hydrogen cannister
- Also connects to 1-Step Pressure Regulator

HOW IT WORKS